



NATIONWIDE PLASTICS, INC.

The Authority on Plastics Manufacturing and Distribution



Containment Glazing Product Data

MAKROLON HYGARD® CG750

MAKROLON HYGARD® CG750 laminate is a three-ply MAKROLON polycarbonate sheet for higher level architectural glazing security applications. MAKROLON HYGARD CG750 laminate features abrasion and UV resistant surfaces for extended service life in harsh environments.


APPLICATIONS

MAKROLON HYGARD CG750 laminate is used in jails, detention facilities, and psychiatric hospitals as containment glazing for protection against forced entry/ egress into or from controlled areas.

Typical Physical Properties

Gauge/Tolerance	.780 ± 5%
Weight	4.9 lbs./s.f.
Shading Coefficient	.87
% Light Transmittance	77% (clear)
Colors	Standard: Clear Custom Colors on request
Sheet Sizes	Standard: 38" x 96" 48" x 96" 60" x 96" Custom Sizes on request

MARKROLON HYGARD CG750 Laminate



Sheffield Plastics Inc. will not be responsible for the use of this information relative to actual application. Users must make their own determination of its suitability for their specific application. No warranty is made for the fitness of any product, and nothing herein waives any of the seller's conditions of sale.

FORCED ENTRY, BALLISTICS RATINGS

H.P. WHITE TP 0500.01 Level IV Step 31
H.P. WHITE TP 0500.01 Level B Ballistics (9mm)
ASTM F 1233 Class IV Step 26

Dallas, Texas (Corporate Offices)
Houston, Texas
Brandon, Mississippi

phone 800-782-1836 / 214-239-3870
phone 800-282-4388 / 713-979-0660
phone 800-457-8623 / 601-825-7919

fax 214-239-3871
fax 713-979-0664
fax 601-825-7109

www.nationwideplastics.net

January 1, 2007 - Version 3.0



Product Data

MAKROLON HYGARD® CG750

GLAZING INFORMATION

- Use of structural security framing systems with equal or greater forced entry and/or ballistics ratings as the selected MAKROLON HYGARD laminate is recommended.
- Size MAKROLON HYGARD laminates to allow for a minimum of 1" edge engagement in the frame, with sufficient rabbet depth for material expansion (approx. 1/16"/ft.).
- Use wet or dry sealants/gaskets that are compatible with polycarbonate.
- Remove protective masking after glazing operations are completed and before prolonged exposure to direct sunlight, moisture, or high temperature.

CLEANING INSTRUCTIONS

- Rinse with clean water to remove abrasive dust and dirt.
- Wash with soap or mild detergent using a sponge or soft cloth. Do not scrub.
- Rinse once more. Dry with a soft cloth or chamois to prevent water spots.
- To remove labels, stickers, or grease, rub gently with a cloth wetted thoroughly in VM & P naphtha or isopropyl alcohol. Wash and rinse. Do not use razor blades, scrapers, or squeegees.

Product Specification

MAKROLON HYGARD CG750 laminate:
Three-ply, clear MAKROLON polycarbonate sheet constructed as follows:

- 1/8" MAKROLON polycarbonate sheet with high AR abrasion-resistant surface
- Polyurethane bonding interlayer
- 1/2" MAKROLON polycarbonate sheet
- Polyurethane bonding interlayer
- 1/8" MAKROLON polycarbonate sheet with high AR abrasion-resistant surface

Material shall have a flexural strength of at least 13,500 psi per ASTM D-790; and shall have AR (high performance abrasion-resistant) surfaces for enhanced service life and resistance to marring. Material shall exhibit a self ignition temperature of 1077°F and a flash ignition temperature of 872°F (ASTM D-1929), and conform with ICBO & BOCA Model Building Codes as a CC-1 rated Approved Light Transmitting Plastic.

For additional information please call the Sheffield Plastics Customer Service at: 800-254-1707.



MAKHYCG7508/03



Sheffield Plastics Inc.

A Bayer MaterialScience Company

119 Salisbury Road
Sheffield, MA 01257
800-254-1707
FAX: 800-457-3553
Web site: sheffieldplastics.com

©Copyright, Sheffield Plastics Inc., 2003 Printed in USA
MAKROLON HYGARD® is a registered trademark of Sheffield Plastics Inc.

Dallas, Texas (Corporate Offices)
Houston, Texas
Brandon, Mississippi

phone 800-782-1836 / 214-239-3870
phone 800-282-4388 / 713-979-0660
phone 800-457-8623 / 601-825-7919

fax 214-239-3871
fax 713-979-0664
fax 601-825-7109